



SEB4-F/N





Item number 49.7079-*

Insulated, rigid, Ø 4 mm, accepting spring-loaded Ø 4 mm plugs with rigid insulating sleeve. Machined brass. Insulation material UL94 V-0. The socket is pressed into pre-drilled panels of plastic, metal, etc. Flat connecting tab 4.8 mmx 0.8 mm.

| Technical data | |
|--------------------------------------|--|
| Diameter of plug system | 4 mm |
| Rated Values | 1000 V, CAT III, 24 A |
| Surface treatment electrical contact | Ni |
| Base material electrical contact | CuZn |
| Standard color(s) * | 20 21 22 23 24 25 27 28 29 |
| Test accessory acc. to | IEC EN 61010-2-030 |
| Remarks | Accessories: Flat connecting receptacles FSH4,8x0,8; Press-in tool MB4-S |
| Approvals | UR |

Data sheet SEB4-F/N 02.2024