


## XSMS-419





Item number 66.9395- \*\*

Highly flexible, with in-line  $\emptyset$  4 mm MULTILAM plug with rigid insulating sleeve on both ends. Test lead with integrated high breaking capacity fuses designed for 1000 V, CAT IV in accordance with IEC/EN 61010-031 and allow for the use of  $\emptyset$  4 mm safety probes and test clips for fuse-protected measurements

The two-part fused connector can be easily unscrewed and accepts a high breaking capacity fuse measuring 6.3 x 32 mmThe fuse is not supplied.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT IV, 8 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Standard color(s) *	21 22 23 24 25 26 27 28
Optional color(s)	29
Lead lengths	100; 150; 200 cm
Lead insulation	SIL
Lead cross section	1,0 mm²
Test accessory acc. to	IEC EN 61010-031
User-Information	I 091
Approvals	UL, CE