



XHB-5000



Item number 66.9427-*

Insulated, rigid, Ø 4 mm for high voltages, to accept test leads XHM-5000 and XHL-5000. For safety reasons, the socket is not compatible with any other Ø 4 mm plugs in our range. Flat connecting tab 4.8 mm x 0.8 mm.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT IV, 10 A
Surface treatment electrical contact	Au
Base material electrical contact	CuZn
Standard color(s) *	21 22 23
Thread	M12x0,75
Test accessory acc. to	IEC EN 61010-031
User-Information	I 079
Remarks	Rated voltage 5'000 V: Output voltage of test instruments, e.g. insulation testers